



PRE-SEPARATION SYSTEMS

**Separate particles before they reach your filter
and increase your collection capacity**

95% Efficient With Submicron Particles

Step 1: Choose your HEC Style

HEC-S

- INCLUDES STANDARD, REINFORCED REMOVABLE DRUM
- ATTACHES TO ANY DRUM, ALLOWING FOR MULTIPLE FILLING CYCLES AND REUSE OF OLD DRUMS
- 3" CASTERS WITH HEAVY DUTY CADDY FOR ULTIMATE MOBILITY



HEC-BG

- 8" AIRTIGHT BLASTGATE DIRECT DISCHARGE OFFERS EASY CONTAINER-FREE DISPOSAL WHILE MINIMIZING CONTACT WITH CONTENTS
- FORK LIFT POCKETS FOR ULTIMATE MOBILITY EVEN UNDER HEAVY LOADS



HEC-DB

- UNIVERSAL DIRECT BAGGING SYSTEM ALLOWS FOR DUSTLESS CLEAN-UP AND MINIMIZES CONTACT WITH CONTENTS
- EXTERNAL GRAVITY DROP FOR CONTINUOUS DISCHARGE AND VACUUM OPERATION
- OVERSIZED INTERNAL DROP OUT CHAMBER WITH VELOCITY BREAK
- 6" HEAVY DUTY CASTERS AND COUNTER-BALANCED BASE FOR ULTIMATE MOBILITY



HEC-XLT

BEST SELLER

- LIFTING ASSEMBLY MECHANICALLY RAISES CYCLONE FROM DRUM FOR EASY EMPTYING
- TIPPING DRUM FOR FAST EMPTYING ELIMINATES ANY HEAVY LIFTING
- FORK LIFT POCKETS FOR ULTIMATE MOBILITY EVEN UNDER HEAVY LOADS
- EQUALIZER KIT ALLOWS PLASTIC BAGS TO BE USED FOR COLLECTION WITHIN DRUM



Step 2: Sizing your HEC

The High Efficiency Cyclone (HEC) system increases your Ruwac vacuum's collection capacity while sparing you from costly filter changes.

Now with these 4 unique HEC Separation Systems, the clean-up process is much easier thanks to an array of benefits such as tipping drums, bagging systems and lifting assemblies. All systems are compatible with the following 8", 12" or 14" HEC units.



HEC8	HEC12	HEC14
8" Diameter	12" Diameter	14" Diameter
100 - 250 CFM	250 - 350 CFM	375 - 525 CFM
2" Inlet	2.75" Inlet	4" Inlet

Step 3: Purchase your HEC

Visit [HEC SERIES](#) and fill out a contact form or

Call **(413)532-4030** to be connected with a sales Representative!



Pre-Separators XLT

All-In-One Vacuum and Pre-Separator

